



# Dissipative Wash Bottles



**35359**



**35436**

**Description**

- Dissipative Yellow Bottle with swan neck spout
- Promotes ESD control awareness
- Used to hold water for wetting sponges at soldering stations, to hold cleaning agents or similar liquids
- Simply squeeze the bottle to release some contents through the spout.
- No Migratory Additives - reduces the chance for contamination from the bottle
- LDPE durAstatic bottles are dissipative; electrostatic charges are removed to ground when handled by a grounded operator or in contact with ESD worksurface
- Highly visible with ESD protective symbol, allowing people to immediately know the bottle is ESD protective
- Available in 8 or 16 ounce Bottle

**Specifications**



Bottle volume resistance  $1 \times 10^4$  to  $< 1 \times 10^{11}$  ohms per ANSI/ESD STM11.12  
Meets ANSI/ESD S20.20, EN 61340-5-1, ANSI/ESD S541 and EN 61340-5-3

<b>35359</b>	<b>35436</b>
<ul style="list-style-type: none"> <li>• Material = LDPE</li> <li>• Size = 8 oz. (240mL)</li> <li>• Base Diameter = 2-1/4" (57mm)</li> <li>• Neck Size = 28-400</li> <li>• Height = 7-3/4" (197mm)</li> </ul>	<ul style="list-style-type: none"> <li>• Material = LDPE</li> <li>• Size = 16 oz. (480mL)</li> <li>• Base Diameter = 2.9" (74mm)</li> <li>• Neck Size = 28-400</li> <li>• Height = 9" (228mm)</li> </ul>

<b>35359</b>	8 oz. (240mL) Bottle, Dissipative LPDE, Yellow
<b>35436</b>	16 oz. (480mL) Bottle, Dissipative LPDE, Yellow

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the ac-tivity." [ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]

If not otherwise noted, tolerances  $\pm 10\%$   
Specifications and procedures subject to change without notice

**durAstatic Dissipative Wash Bottles**

<b>MENDA</b> 3651 WALNUT AVE., CHINO, CA 91710 PHONE: (909) 627-2453 WEBSITE: MendaPump.com	<b>DRAWING NUMBER</b> 35359	<b>DATE:</b> May 2016
--	--------------------------------	--------------------------

© 2016 DESCO INDUSTRIES INC.  
Employee Owned